



ALDOA Antibody [2E6]

CATALOG NUMBER: 70-181

Specifications

| | |
|-----------------------------|---|
| SPECIES REACTIVITY: | Human, Mouse |
| TESTED APPLICATIONS: | ELISA, IHC, WB |
| APPLICATIONS: | ALDOA Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 5 ug/mL and Western Blot starting at 1:500 - 1:1000. |
| USER NOTE: | Optimal dilutions for each application to be determined by the researcher. |
| IMMUNOGEN: | Recombinant protein |
| HOST SPECIES: | Mouse |

Properties

| | |
|----------------------------|--|
| PURIFICATION: | Protein A Column |
| PHYSICAL STATE: | Liquid |
| BUFFER: | PBS, pH 7.4. Sourced in Ascites. |
| STORAGE CONDITIONS: | ALDOA Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles. |
| CLONALITY: | Monoclonal |
| ISOTYPE: | IgG2a,k |
| CONJUGATE: | Unconjugated |

Additional Info

| | |
|-------------------------|---|
| ALTERNATE NAMES: | ALDOA, ALDA, Aldolase, GSD12, Muscle-type aldolase, Lung cancer antigen NY-LU-1 |
| ACCESSION NO.: | P04075 |
| PROTEIN GI NO.: | 113606 |
| OFFICIAL SYMBOL: | ALDOA |
| GENE ID: | 226 |

Background

FOR RESEARCH USE ONLY

December 13, 2016