



Adiponectin Antibody

CATALOG NUMBER: 54-200

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	Adiponectin antibody can be used at 1:2000-1:5000 dilutions for Western Blot analysis and for other immunoassays. Customers need to optimize the dilution when using the antibody in IHC or ICC.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Adiponectin antibody reacts with Adiponectin protein (about 30 kDa) of human, mouse, rat and may cross-react with Adiponectin protein of other mammalian species.
IMMUNOGEN:	Human and mouse Adiponectin C-terminus peptide
HOST SPECIES:	Chicken

Properties

PURIFICATION:	Affinity Purified
PHYSICAL STATE:	Liquid
BUFFER:	PBS Buffer containing 0.02% sodium azide.
STORAGE CONDITIONS:	2-8°C for one week and -20°C as an undiluted liquid for up to two years.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ACDC, ACRP30, APM1, GBP28, Adiponectin, 30 kDa adipocyte complement-related protein, ADPN, APM-1, ADIPQTL1
ACCESSION NO.:	NP_004788.1
PROTEIN GI NO.:	4757760
OFFICIAL SYMBOL:	ADIPOQ
GENE ID:	9370

Background

FOR RESEARCH USE ONLY

December 13, 2016