



## GPR177 Antibody

CATALOG NUMBER: 54-212

### Specifications

<b>SPECIES REACTIVITY:</b>	Human, Mouse
<b>TESTED APPLICATIONS:</b>	WB
<b>APPLICATIONS:</b>	GPR177 antibody can be used at 1:2,000 to 1:5,000 for immunoblot testing. User needs to optimize the concentrations in assay.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>SPECIFICITY:</b>	GPR177 antibody binds to a strong band at about 55 kDa on HEK293 cell line, the apparent MW may be bigger or smaller. The product may cross react with GPR177 from other mammalian species.
<b>IMMUNOGEN:</b>	Human GPR177 C-terminus peptide
<b>HOST SPECIES:</b>	Chicken

### Properties

<b>PURIFICATION:</b>	Affinity Purified
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS Buffer containing 0.02% sodium azide.
<b>STORAGE CONDITIONS:</b>	2-8°C for one week and -20°C as an undiluted liquid for up to two years.
<b>CLONALITY:</b>	Polyclonal
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	G Protein-Coupled Receptor 177, C1orf139, GPR177, UNQ85/PRO18667, Protein wntless homolog, Integral membrane protein GPR177, EVI, MRP, mig-14
<b>ACCESSION NO.:</b>	NP_079187.3 / NP_080858.3
<b>PROTEIN GI NO.:</b>	31542745 / 98986316
<b>OFFICIAL SYMBOL:</b>	WLS
<b>GENE ID:</b>	79971

### Background

FOR RESEARCH USE ONLY

December 13, 2016