



ACAT1 Antibody [AT1.H11]

CATALOG NUMBER: 70-185

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ACAT1 Monoclonal Antibody can be used for ELISA starting at 1:2000, immunohistochemistry (tested on paraffin embedded tissues) starting at 10 ug/mL and Western Blot starting at 1:1000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Recognize specifically human ACAT1. Other species not tested.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Immunoaffinity purified
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.4, 0.05% sodium azide
STORAGE CONDITIONS:	ACAT1 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ACAT1, ACAT, Acetoacetyl-CoA thiolase, Acetyl-CoA acetyltransferase 1, MAT, T2, THIL
ACCESSION NO.:	P24752
PROTEIN GI NO.:	135755
OFFICIAL SYMBOL:	ACAT1
GENE ID:	38

Background

FOR RESEARCH USE ONLY

December 13, 2016