



KRT10 / Cytokeratin 10 Antibody

CATALOG NUMBER: 70-513

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	ELISA, IF, IHC-P (1:200), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Keratin 10 Antibody detects endogenous levels of total Keratin 10 protein.
IMMUNOGEN:	Synthetic peptide from human Keratin 10.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	KRT10, BIE, BCIE, CK10, Cytokeratin 10, Cytokeratin-10, EHK, Keratin-10, KPP, Keratin 10, CK-10, K10
ACCESSION NO.:	P13645
PROTEIN GI NO.:	269849769
OFFICIAL SYMBOL:	KRT10
GENE ID:	3858

Background

FOR RESEARCH USE ONLY

December 13, 2016