



Herpes Virus (type 6) Antibody [2002]

CATALOG NUMBER: 35-552

Specifications

SPECIES REACTIVITY:	Virus
TESTED APPLICATIONS:	IF, IHC, IP, WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Specific for the 60/110 KDa envelope glycoprotein of HHV6.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Herpes Virus (type 6) antibody is purified from ascites fluid or culture medium by protein A chromatography or sequential differential precipitations.
PHYSICAL STATE:	Liquid
BUFFER:	Herpes Virus antibody (type 6) is in a phosphate saline buffer (0.01M, pH 7.2) containing 0.1% sodium azide preservative. No stabilizing proteins have been added.
STORAGE CONDITIONS:	Herpes Virus (type 6) antibody can be stored at -20°C, stable for one year.
CLONALITY:	Monoclonal
ISOTYPE:	Mouse IgG2b
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	Anti-Herpes Virus (type 6)
-------------------------	----------------------------

Background

FOR RESEARCH USE ONLY

December 12, 2016