



Cezanne 2 Antibody

CATALOG NUMBER: 46-823

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: Antibody detection limit dilution 1:1,000.

IMMUNOGEN: Cezanne 2 antibody was raised against a 15 amino acid synthetic peptide near the internal region of Cezanne 2.

HOST SPECIES: Goat

Properties

PURIFICATION: Cezanne 2 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: Cezanne 2 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: OTUD7A, OTU domain containing 7A, C15orf16, CEZANNE2, OTUD7, cezanne 2

ACCESSION NO.: NP_570971.1

PROTEIN GI NO.: 18702331

OFFICIAL SYMBOL: OTUD7A

GENE ID: 161725

Background

REFERENCES: 1) Bellone RR, Brooks SA, Sandmeyer L, Murphy BA, Forsyth G, Archer S, Bailey E, Grahn B. Differential gene expression of TRPM1, the potential cause of congenital stationary night blindness and coat spotting patterns (LP) in the Appaloosa horse (*Equus caballus*). *Genetics*. 2008 Aug;179(4):1861-70. Epub 2008 Jul 27.

FOR RESEARCH USE ONLY

December 13, 2016