



prosci-inc.com



ProSci Incorporated
12170 Flint Place
Poway, CA 92064



Toll Free: +1 (888) 513 9525
Local: +1 (858) 513 2638
Fax: +1 (858) 513 2692

techsupport@prosci-inc.com

Parvovirus B19 Antibody [5181]

CATALOG NUMBER: 35-608

Specifications

SPECIES REACTIVITY:	Virus
TESTED APPLICATIONS:	ELISA, IF, WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Specific to human Parvovirus (B19).
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Parvovirus B19 antibody is purified from ascites fluid or culture medium by protein A chromatography or sequential differential precipitations.
PHYSICAL STATE:	Liquid
BUFFER:	Parvovirus B19 antibody is in a phosphate saline buffer (0.01M, pH 7.2) containing 0.1% sodium azide preservative. No stabilizing proteins have been added.
STORAGE CONDITIONS:	Parvovirus B19 antibody can be stored at -20°C, stable for one year.
CLONALITY:	Monoclonal
ISOTYPE:	Mouse IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	Anti-Parvovirus B19
-------------------------	---------------------

Background

FOR RESEARCH USE ONLY

December 12, 2016