




KSHVORF62 Antibody [5B7B6]

CATALOG NUMBER: 32-229



Western blot analysis using KSHV ORF62 monoclonal antibody against KSHV ORF62 recombinant protein



Immunocytochemistry staining of TPA - induced BCBL - 1 cells using monoclonal antibody 5B7B6 clone to KSHV ORF62. HRP - anti - mouse was used as the second antibody before color development with AEC.

Specifications

| | |
|-----------------------------|--|
| SPECIES REACTIVITY: | Virus |
| TESTED APPLICATIONS: | WB |
| APPLICATIONS: | Western Blot:1:500 - 1,000 ELISA:Determining optimal working dilutions by titration test. |
| USER NOTE: | Optimal dilutions for each application to be determined by the researcher. |
| IMMUNOGEN: | Ni-NTA purified recombinant human KSHV ORF62 expressed in E. Coli strain BL21 (DE3). |
| HOST SPECIES: | Mouse |

Properties

| | |
|----------------------------|---|
| BUFFER: | Ascitic fluid containing 0.03% sodium azide. |
| STORAGE CONDITIONS: | to KSHV ORF62 monoclonal antibody can be stored at -20°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures. |
| CLONALITY: | Monoclonal |
| ISOTYPE: | IgM |
| CONJUGATE: | Unconjugated |

Additional Info

| | |
|-------------------------|--------------------------------------|
| ALTERNATE NAMES: | Triplex capsid protein VP19C homolog |
| ACCESSION NO.: | F5H8Y5 |
| PROTEIN GI NO.: | 550600169 |
| OFFICIAL SYMBOL: | ORF62 |
| GENE ID: | 4961461 |

Background

REFERENCES:

1) Chang Y. et al. 1994. Science. 266:1865-1869.

2) Russo J.J. et al. 1996. PNAS. 93: 14862-14867.

3) Wu L. et al. 2000. J VirolOct; 74(20):9646-54.

FOR RESEARCH USE ONLY

December 12, 2016