



NGFRAP1 Antibody

CATALOG NUMBER: 46-876

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: Antibody detection limit dilution 1:8,000.

SPECIFICITY: This antibody is expected to recognise isoform a (NP_996800.1) and isoform b (NP_996798.1 and NP_055195.1).

IMMUNOGEN: NGFRAP1 antibody was raised against a 15 amino acid synthetic peptide near the C-Terminus of NGFRAP1.

HOST SPECIES: Goat

Properties

PURIFICATION: NGFRAP1 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: NGFRAP1 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: NGFRAP1, nerve growth factor receptor (TNFRSF16) associated protein 1, RP13-349O20.1, BEX3, Bex, DXS6984E, HGR74, NADE, ovarian granulosa cell protein (13kD), p75NTR-associated cell death executor

ACCESSION NO.: NP_996800.1, NP_996798.1, NP_055195.1

PROTEIN GI NO.: 46094062

OFFICIAL SYMBOL: NGFRAP1

GENE ID: 27018

Background

REFERENCES: 1) Passino MA, Adams RA, Sikorski SL, Akassoglou K. Regulation of hepatic stellate cell differentiation by the neurotrophin receptor p75NTR. Science. 2007 Mar 30;315(5820):1853-6.

FOR RESEARCH USE ONLY

December 13, 2016