




CDKN2A Antibody [1E12E10]

CATALOG NUMBER: 51-657



Immunohistochemistry of human colon
crypt tissue stained using CDKN2A
Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	CDKN2A antibody can be used in ELISA starting at 1:000 - 1:1000, and immunohistochemistry starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Ni-NTA purified truncated recombinant P16 expressed in E. Coli strain BL21 (DE3)
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Affinity Chromatography
PHYSICAL STATE:	Liquid
STORAGE CONDITIONS:	Store CDKN2A antibody at 4 °C or -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CDKN2A, ARF, Cdk4 inhibitor, CDK4 inhibitor p16-INK4, INK4, INK4A, Multiple tumor suppressor 1, MTS-1, MTS1, p16-INK4, p16-INK4A, p16INK4, p19, p14, p16, p16 INK4A, p16INK4A, p14ARF, TP16, CDK4I, CDKN2, CMM2, MLM, p19ARF
ACCESSION NO.:	P42771
PROTEIN GI NO.:	3041660
OFFICIAL SYMBOL:	CDKN2A
GENE ID:	1029

Background

