



USP6 Antibody

CATALOG NUMBER: 43-030

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:4000. Western Blot: Preliminary experiments in Human Testis, Prostate and Placenta lysates gave no specific signal but low background (at antibody concentration up to 1ug/ml). We would appreciate any feedback from people in the field - have any results been re

SPECIFICITY: This antibody is expected NOT to cross react to USP32 or to the TBC1D3 proteins.

IMMUNOGEN: USP6 antibody was raised against a 14 amino acid peptide near the internal region (near N Terminus) of USP6 (aa142-155).

HOST SPECIES: Goat

Properties

PURIFICATION: USP6 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: USP6 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: deubiquitinating enzyme 6, HRP1, hyperpolymorphic gene 1, OTTHUMP00000125301, proto-oncogene TRE-2, TRE17, TRE2, Tre-2, tre-2 oncogene, ubiquitin carboxyl-terminal hydrolase 6, ubiquitin specific peptidase 6-, ubiquitin specific peptidase 6 (Tre-2 oncogene), ubiquitin specific protease 6 (Tre-2 oncogene), ubiquitin thioesterase 6, ubiquitin thiolesterase 6, ubiquitin-specific protease USP6, ubiquitin-specific-processing protease 6, USP6, USP6-short

ACCESSION NO.: NP_004496.2

PROTEIN GI NO.: 109638751

OFFICIAL SYMBOL: USP6

GENE ID: 9098

Background

FOR RESEARCH USE ONLY