



ADAMTS8 Antibody

CATALOG NUMBER: 42-546

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:32000. Western Blot: Preliminary experiments in Human Brain (Cerebellum), Lung and Placenta lysates gave no specific signal but low background (at antibody concentration up to 1 ug/ml). We would appreciate any feedback from people in the field - have any results

IMMUNOGEN: ADAMTS8 antibody was raised against a 10 amino acid synthetic peptide near the internal region of ADAMTS8.

HOST SPECIES: Goat

Properties

PURIFICATION: ADAMTS8 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: ADAMTS8 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: ADAMTS8, METH2, FLJ41712, ADAM-TS8, ADAM metalloproteinase with thrombospondin type 1 motif, 8, a disintegrin-like and metalloprotease (reprolysin type) with thrombospondin type 1 motif

ACCESSION NO.: NP_008968.4

PROTEIN GI NO.: 153792351

OFFICIAL SYMBOL: ADAMTS8

GENE ID: 11095

Background

FOR RESEARCH USE ONLY

December 13, 2016