




AHR Antibody [3B9]

CATALOG NUMBER: 51-879



Immunohistochemistry of human placenta
tissue stained using AHR Monoclonal
Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC
APPLICATIONS:	AHR antibody can be used in immunohistochemistry starting at 5 ug/mL, and flow cytometry.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	AHR (NP_001612, 279 a.a. ~ 376 a.a) full length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	Aliquot and store AHR antibody at -20 °C or -80 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	AHR, Ah receptor, AH-receptor, Aryl hydrocarbon receptor, BHLHe76, Aromatic hydrocarbon receptor
ACCESSION NO.:	P35869
PROTEIN GI NO.:	3041653
OFFICIAL SYMBOL:	AHR
GENE ID:	196

Background

