




CD3-Zeta Antibody [4A12-F6]

CATALOG NUMBER: 51-898



Immunohistochemistry of human spleen tissue stained using CD3-Zeta Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, IP, WB
APPLICATIONS:	CD3-Zeta antibody can be used in immunohistochemistry starting at 10 ug/mL, and flow cytometry starting at 1 ug/1E6 cells.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	CD3Z (AAH25703, 1 a.a. ~ 165 a.a) full length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
CONCENTRATION:	0.44 mg/ml
STORAGE CONDITIONS:	Aliquot and store CD3-Zeta antibody at -20 °C or -80 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CD247, CD3 Zeta, CD3H, CD3Z, CD247 antigen, zeta subunit, CD247 molecule, CD3zeta chain, T3Z, TCR zeta chain, TCRZ, T-cell receptor T3 zeta chain, CD247 antigen, CD3-ZETA, CD3Q
ACCESSION NO.:	P20963
PROTEIN GI NO.:	23830999
OFFICIAL SYMBOL:	CD247
GENE ID:	919

