



CLEC16A Antibody

CATALOG NUMBER: 42-088



Western blot analysis of CLEC16A in human liver lysate (35 ug protein in RIPA buffer) using CLEC16A Antibody at 2 ug/mL.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	ELISA: Antibody detection limit dilution 1:1000. Western Blot: Approximately 110 kDa band observed in human kidney and liver lysates (calculated MW of 118 kDa according to NP_056041.1). Recommended concentration: 1-3 ug/mL.
POSITIVE CONTROL:	1) Cat. No. 1304 - Human Liver Tissue Lysate
IMMUNOGEN:	CLEC16A antibody was raised against a 14 amino acid synthetic peptide near the C-Terminus of CLEC16A.
HOST SPECIES:	Goat

Properties

PURIFICATION:	CLEC16A antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
PHYSICAL STATE:	Liquid
BUFFER:	CLEC16A antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
CONCENTRATION:	500 ug/mL
STORAGE CONDITIONS:	Aliquot and store at -20°C. Minimize freezing and thawing.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	MGC111457, KIAA0350, Gop-1, C-type lectin domain family 16, member A, CLEC16A
ACCESSION NO.:	NP_056041.1
PROTEIN GI NO.:	54792782
OFFICIAL SYMBOL:	CLEC16A
GENE ID:	23274

