




CDH17 Antibody [3H2]

CATALOG NUMBER: 51-900



Immunohistochemistry of human small intestine tissue stained using CDH17 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	CDH17 antibody can be used in immunohistochemistry starting at 10 ug/mL, and flow cytometry starting at 0.5 µg/1E6 cells.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	CDH17 (NP_004054, 24 a.a. ~ 132 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
CONCENTRATION:	0.28 mg/ml
STORAGE CONDITIONS:	Aliquot and store CDH17 antibody at -20 °C or -80 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CDH17, Cadherin 16, Cadherin-16, HPT1, Human peptide transporter 1, LI cadherin, HPT-1, HPT-1 cadherin, BILL-cadherin, Cadherin, Cadherin-17, LI-cadherin, Liver-intestine cadherin
ACCESSION NO.:	Q12864
PROTEIN GI NO.:	308153624
OFFICIAL SYMBOL:	CDH17
GENE ID:	1015

