




Factor 10 Antibody

CATALOG NUMBER: 51-988



Immunohistochemistry of human vessels tissue stained using Factor 10 Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	Factor 10 antibody can be used in Western Blot starting at 1 - 3 ug/mL, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Purified protein
HOST SPECIES:	Sheep

Properties

PURIFICATION:	Ammonium Sulfate Precipitation
PHYSICAL STATE:	Liquid
BUFFER:	50% glycerol
STORAGE CONDITIONS:	Factor 10 antibody may be stored at 4 °C for short-term only. As with all antibodies avoid freeze/thaw cycles. Store at -20 °C for long term. Aliquots are stable for at least 12 months
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	F10, Factor X, FX, Factor X deficiency, Stuart factor, Stuart-Prower factor, Coagulation factor X, Factor Xa, FXA, Prothrombinase
ACCESSION NO.:	P00742
PROTEIN GI NO.:	119761
OFFICIAL SYMBOL:	F10
GENE ID:	2159

Background

FOR RESEARCH USE ONLY

