



GRAMD3 Antibody

CATALOG NUMBER: 42-324

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA, WB

APPLICATIONS: ELISA: Antibody detection limit dilution 1:1000. Western Blot: Preliminary experiments in human frontal cortex, spleen and placenta lysates gave no specific signal but low background (at antibody concentration up to 1 ug/mL).

SPECIFICITY: This antibody is expected to recognize all reported isoforms (NP_001139791.1; NP_076416.2; NP_001139792.1; NP_001139793.1; NP_001139794.1).

IMMUNOGEN: GRAMD3 antibody was raised against a 10 amino acid synthetic peptide near the internal region of GRAMD3.

HOST SPECIES: Goat

Properties

PURIFICATION: GRAMD3 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: GRAMD3 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: GRAMD3, NS3TP2, hepatitis C virus nonstructural protein 3-transactivating protein 2, HCV NS3-transactivated protein 2, GRAM domain containing 3, FLJ21313

ACCESSION NO.: NP_001139791.1, NP_076416.2, NP_001139792.1, NP_001139793.1, NP_001139794.1

PROTEIN GI NO.: 226443011

OFFICIAL SYMBOL: GRAMD3

GENE ID: 65983

Background

FOR RESEARCH USE ONLY

December 13, 2016