




EBI3 Antibody [DNT27]

CATALOG NUMBER: 70-021



Immunohistochemistry of human lymphoid-dendritic cells stained using EBI3 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	EBI3 antibody can be used in ELISA, Western Blot, immunohistochemistry starting at 5 ug/mL, and immunofluorescence starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Mouse EBI3
HOST SPECIES:	Rat

Properties

PURIFICATION:	Affinity Purified
PHYSICAL STATE:	Liquid
BUFFER:	Aqueous buffer, 0.09% sodium azide, contains stabilizer if necessary
STORAGE CONDITIONS:	Store EBI3 antibody at 4 °C. As with all antibodies avoid freeze/thaw cycles
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	EBI3, Epstein-Barr virus induced 3, IL-27 subunit beta, IL27 subunit, IL27B, Interleukin-27 subunit beta, IL-27B, Cytokine receptor, EBV-induced gene 3 protein, IL35 subunit
ACCESSION NO.:	Q14213
PROTEIN GI NO.:	47605806
OFFICIAL SYMBOL:	EBI3
GENE ID:	10148

Background

