



DUBA2 Antibody

CATALOG NUMBER: 42-136

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	ELISA: Antibody detection limit dilution 1:64000. Western Blot: Approximately 22-23 kDa band in human pancreas, human ovary and human kidney lysates after 1 ug/mL antibody staining. The 23 kDa band was successfully blocked by incubation with the immunizing peptide.
IMMUNOGEN:	DUBA2 antibody was raised against a 14 amino acid synthetic peptide near the internal region of DUBA2.
HOST SPECIES:	Goat

Properties

PURIFICATION:	DUBA2 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
PHYSICAL STATE:	Liquid
BUFFER:	DUBA2 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
CONCENTRATION:	500 ug/mL
STORAGE CONDITIONS:	Aliquot and store at -20°C. Minimize freezing and thawing.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	DUBA2, HIN-6 protease, HSHIN6, FLJ25831, DUBA2, OTU domain containing 6A, OTUD6A
ACCESSION NO.:	NP_997203.1
PROTEIN GI NO.:	46409282
OFFICIAL SYMBOL:	OTUD6A
GENE ID:	139562

Background

REFERENCES:	1) Donaghue C, Bates H, Cotterill S Identification and characterisation of the Drosophila homologue of the yeast Uba2 gene Biochim Biophys Acta. 2001 Mar 19;1518(1-2):210-4
--------------------	--

FOR RESEARCH USE ONLY

December 13, 2016