



CALB1 Antibody, Monoclonal

CATALOG NUMBER: 70-105

Specifications

SPECIES REACTIVITY:	Mouse, Rat
TESTED APPLICATIONS:	IHC, IP, WB
APPLICATIONS:	CALB1 Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 1:100 and Western Blot starting at 1:1000 - 1:2000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Purified
PHYSICAL STATE:	Liquid
BUFFER:	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
STORAGE CONDITIONS:	CALB1 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CALB1, Calbindin D28, Calbindin, Calbindin 1, 28kDa, CAB27, CALB, RTVL-H protein, Calbindin 1, (28kD), D-28K
ACCESSION NO.:	P05937
PROTEIN GI NO.:	115394
OFFICIAL SYMBOL:	CALB1
GENE ID:	793

Background

FOR RESEARCH USE ONLY

December 13, 2016