



SKA3 Antibody

CATALOG NUMBER: 42-185

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	ELISA: Antibody detection limit dilution 1:64000. Western Blot: Approximately 35 kDa and 150 kDa band in HeLa lysates after 2 ug/mL antibody staining. Both bands were successfully blocked by incubation with the immunizing peptide.
IMMUNOGEN:	SKA3 antibody was raised against a 13 amino acid synthetic peptide near the internal region of SKA3.
HOST SPECIES:	Goat

Properties

PURIFICATION:	SKA3 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
PHYSICAL STATE:	Liquid
BUFFER:	SKA3 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
CONCENTRATION:	500 ug/mL
STORAGE CONDITIONS:	Aliquot and store at -20°C. Minimize freezing and thawing.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	SKA3, SKA3, RAMA1, MGC4832, chromosome 13 open reading frame 3, C13orf3
ACCESSION NO.:	NP_659498.3
PROTEIN GI NO.:	156523260
OFFICIAL SYMBOL:	C13orf3
GENE ID:	221150

Background

REFERENCES:	1) Theis M, Slabicki M, Junqueira M, Paszkowski-Rogacz M, Sontheimer J, Kittler R, Heninger AK, Glatter T, Kruusmaa K, Poser I, Hyman AA, Pisabarro MT, Gstaiger M, Aebersold R, Shevchenko A, Buchholz F. Comparative profiling identifies C13orf3 as a component of the Ska complex required for mammalian cell division. The EMBO journal 2009 May 28 (10): 1453-65.
--------------------	---

FOR RESEARCH USE ONLY

December 13, 2016