



SLCO1B3 Antibody

CATALOG NUMBER: 42-218

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: Antibody detection limit dilution 1:2000.

IMMUNOGEN: SLCO1B3 antibody was raised against an 11 amino acid synthetic peptide near the internal region of SLCO1B3.

HOST SPECIES: Goat

Properties

PURIFICATION: SLCO1B3 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: SLCO1B3 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: SLCO1B3, solute carrier family 21 (organic anion transporter), member 8, organic anion transporter LST-3c, liver-specific organic anion transporter 3TM13, SLC21A8, OATP8, OATP1B3, LST3, LST-3TM13, solute carrier organic anion transporter family, member 1B3, SLCO1B3, HBLRR, LST-2, OATP-8

ACCESSION NO.: NP_062818.1

PROTEIN GI NO.: 9790233

OFFICIAL SYMBOL: SLCO1B3

GENE ID: 28234

Background

REFERENCES: 1) Aoki M, Terada T, Ogasawara K, Katsura T, Hatano E, Ikai I, Inui K, Impact of regulatory polymorphisms in organic anion transporter genes in the human liver. Pharmacogenetics and genomics 2009 Aug 19 (8): 647-56.

FOR RESEARCH USE ONLY

December 13, 2016