



## TNFRSF18 Antibody [2H4]

CATALOG NUMBER: 70-160

### Specifications

<b>SPECIES REACTIVITY:</b>	Human, Mouse
<b>TESTED APPLICATIONS:</b>	ELISA, IHC, WB
<b>APPLICATIONS:</b>	TNFRSF18 Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 5 ug/mL and Western Blot starting at 1:500 - 1:1000.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	Recombinant protein
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Protein A Column
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS, pH 7.2
<b>CONCENTRATION:</b>	1 mg/ml
<b>STORAGE CONDITIONS:</b>	TNFRSF18 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG2b,k
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	TNFRSF18, AITR, CD357, CD357 antigen, GITR, GITR-D
<b>ACCESSION NO.:</b>	Q9Y5U5
<b>PROTEIN GI NO.:</b>	13878830
<b>OFFICIAL SYMBOL:</b>	TNFRSF18
<b>GENE ID:</b>	8784

### Background

FOR RESEARCH USE ONLY

December 13, 2016