



AIFM3 Antibody

CATALOG NUMBER: 42-278

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: Antibody detection limit dilution 1:64000.

SPECIFICITY: This antibody is expected to recognize all isoforms (NP_653305.1; NP_001018070.1, NP_001139760.1).

IMMUNOGEN: AIFM3 antibody was raised against a 15 amino acid synthetic peptide near the internal region of AIFM3.

HOST SPECIES: Goat

Properties

PURIFICATION: AIFM3 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: AIFM3 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: AIFM3, AIFL

ACCESSION NO.: NP_653305.1, NP_001018070.1, NP_001139760.1

PROTEIN GI NO.: 21389617

OFFICIAL SYMBOL: AIFM3

GENE ID: 150209

Background

REFERENCES: 1) Ashktorab H, Dashwood RH, Dashwood MM, Zaidi SI, Hewitt SM, Green WR, Lee EL, Darempouran M, Nouraie M, Malekzadeh R, Smoot DT. H. pylori-induced apoptosis in human gastric cancer cells mediated via the release of apoptosis-inducing factor from mitochondria. *Helicobacter* 2008 Dec 13 (6): 506-17.

FOR RESEARCH USE ONLY

December 13, 2016