



CREBBP Antibody, Monoclonal

CATALOG NUMBER: 70-202

Specifications

SPECIES REACTIVITY:	Human, Monkey, Mouse, Rat
TESTED APPLICATIONS:	IF, IHC
APPLICATIONS:	CREBBP Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 1:25.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Recognizes p300 and CBP
IMMUNOGEN:	Purified p300 protein. Epitope: aa2071-2091.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.4, 0.2% BSA, 0.09% sodium azide, before the addition of glycerol to 40%.
STORAGE CONDITIONS:	CREBBP Monoclonal antibody may be stored at 4°C; Avoid freeze-thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2b
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CREBBP, CREB binding protein, CREB-binding protein, KAT3A, RSTS, Rubinstein-Taybi syndrome, RTS, CBP
ACCESSION NO.:	Q92793
PROTEIN GI NO.:	116241283
OFFICIAL SYMBOL:	CREBBP
GENE ID:	1387

Background

FOR RESEARCH USE ONLY

December 13, 2016