



TXNDC11 Antibody

CATALOG NUMBER: 42-402



Western Blot (1ug/ml) staining of Human Thymus lysate (35ug protein in RIPA buffer). Primary incubation was 1 hour. Detected by chemiluminescence.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	ELISA: antibody detection limit dilution 1:16000. Western Blot: Approx 100kDa band observed in Human Spleen and Thymus lysates (calculated MW of 108kDa according to NP_056998.4). Recommended concentration: 1-3ug/ml.
POSITIVE CONTROL:	1) Cat. No. 1306 - Human Spleen Tissue Lysate 2) Cat. No. 1314 - Human Thymus Tissue Lysate
IMMUNOGEN:	TXNDC11 antibody was raised against a amino acid synthetic peptide near the of TXNDC11 (aa 113-126).
HOST SPECIES:	Goat

Properties

PURIFICATION:	TXNDC11 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
PHYSICAL STATE:	Liquid
BUFFER:	TXNDC11 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
CONCENTRATION:	500 ug/mL
STORAGE CONDITIONS:	Aliquot and store at -20°C. Minimize freezing and thawing.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	thioredoxin domain-containing protein 11, EF-hand-binding protein 1, EF-hand binding protein 1, EFP1, thioredoxin domain containing 11, TXNDC11
ACCESSION NO.:	NP_056998.4
PROTEIN GI NO.:	54633317

OFFICIAL SYMBOL: TXNDC11

GENE ID: 51061

Background

FOR RESEARCH USE ONLY

December 13, 2016