



## F8 Antibody

CATALOG NUMBER: 70-278

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	ELISA, GS, IHC
<b>APPLICATIONS:</b>	F8 antibody can be used for staining paraffin embeded tissues starting at 5 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>SPECIFICITY:</b>	Recognizes human F. VIII as demonstrated by immunodiffusion and ELISA. No reactivity was observed with von Willebrand Factor.
<b>IMMUNOGEN:</b>	Human Factor VIIIc (F. VIII) purified from F. VIII concentrate.
<b>HOST SPECIES:</b>	Sheep

### Properties

<b>PURIFICATION:</b>	Ammonium Sulfate Precipitation
<b>STORAGE CONDITIONS:</b>	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
<b>CLONALITY:</b>	Polyclonal
<b>ISOTYPE:</b>	IgG
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	F8, AHF, Antihemophilic factor, Coagulation factor VIIIc, Coagulation factor VIII, DXS1253E, Factor VIII F8B, FVIII, HEMA, F8B, Factor VIII, Procoagulant component, F8C
<b>ACCESSION NO.:</b>	P00451
<b>PROTEIN GI NO.:</b>	119767
<b>OFFICIAL SYMBOL:</b>	F8
<b>GENE ID:</b>	2157

### Background

**FOR RESEARCH USE ONLY**

December 13, 2016