




ASNSD1 Antibody

CATALOG NUMBER: 42-435



HEK293 lysate (10ug protein in RIPA buffer) overexpressing Human ASNSD1 with DYKDDDDK tag probed with antibody (1ug/ml) in Lane A and probed with anti-DYKDDDDK Tag (1/10000) in lane C. Mock-transfected HEK293 probed with antibody (1mg/ml) in Lane B. Primary

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	ELISA: antibody detection limit dilution 1:16000. Western Blot: In transfected HEK293 transiently expressing full-length Human ASNSD1 (myc and DYKDDDDK tagged), a band of approx. 75kDa was observed. No bands were observed in mock-transfected HEK293 and the same band was observed using anti-myc tag antib
POSITIVE CONTROL:	1) Transfected HEK293
IMMUNOGEN:	ASNSD1 antibody was raised against a 10 amino acid synthetic peptide near the internal region of ASNSD1.
HOST SPECIES:	Goat

Properties

PURIFICATION:	ASNSD1 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
PHYSICAL STATE:	Liquid
BUFFER:	ASNSD1 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
CONCENTRATION:	500 ug/mL
STORAGE CONDITIONS:	Aliquot and store at -20°C. Minimize freezing and thawing.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ASNSD1, NS3TP1, NBLA00058, HCV NS3-transactivated protein 1, FLJ20752, asparagine synthetase domain containing 1, Nbla00058
ACCESSION NO.:	NP_061921.1

PROTEIN GI NO.: 9506697

OFFICIAL SYMBOL: ASNSD1

GENE ID: 54529

Background

FOR RESEARCH USE ONLY

December 13, 2016