



TRIP6 Antibody

CATALOG NUMBER: 42-550



Western Blot (2ug/ml) staining of K562 lysate (35ug protein in RIPA buffer). Primary incubation was 1 hour. Detected by chemiluminescence.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	ELISA: antibody detection limit dilution 1:16000. Western Blot: Approx 50kDa band observed in lysates of cell line K562 (calculated MW of 50.3kDa according to NP_003293.2). Recommended concentration: 1-3ug/ml.
POSITIVE CONTROL:	1) Cat. No. 1204 - K562 Cell Lysate
IMMUNOGEN:	TRIP6 antibody was raised against a 12 amino acid synthetic peptide near the internal region of TRIP6.
HOST SPECIES:	Goat

Properties

PURIFICATION:	TRIP6 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
PHYSICAL STATE:	Liquid
BUFFER:	TRIP6 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
CONCENTRATION:	500 ug/mL
STORAGE CONDITIONS:	Aliquot and store at -20°C. Minimize freezing and thawing.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	TRIP6, zyxin related protein 1, ZRP-1, thyroid receptor-interacting protein 6, thyroid hormone receptor interactor 6, OPA-interacting protein 1, OIP1, MGC4423, MGC3837, MGC29959, MGC10558, MGC10556
ACCESSION NO.:	NP_003293.2
PROTEIN GI NO.:	91208423
OFFICIAL SYMBOL:	TRIP6
GENE ID:	7205

