




C5AR Antibody, Monoclonal

CATALOG NUMBER: 48-012



Human placenta tissue stained with C5AR1 Antibody at 10 ug/mL followed by biotinylated anti-mouse IgG secondary antibody, alkaline phosphatase-streptavidin and chromogen.

Specifications

SPECIES REACTIVITY:	Human, Rabbit
TESTED APPLICATIONS:	FACS, IHC, Neut
APPLICATIONS:	C5AR antibody can be used in Western Blot starting at 1 - 2 ug/mL, and immunohistochemistry starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Recognizes the C5a receptor (C5aR) CD88, which is predominantly expressed on cells of the myeloid lineage.
IMMUNOGEN:	C5aR - peptide: Met1 - Asn31.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Ion Exchange Chromatography
PHYSICAL STATE:	Liquid
BUFFER:	PBS. Supplied azide free
STORAGE CONDITIONS:	Store C5AR antibody at 4 °C or -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	C5AR1, C5A, C5a-R, C5a ligand, C5a receptor, CD88, C5a anaphylatoxin receptor, C5AR, C5R1, CD88 antigen
ACCESSION NO.:	P21730
PROTEIN GI NO.:	311033355
OFFICIAL SYMBOL:	C5AR1
GENE ID:	728

