



PRDM10 Antibody

CATALOG NUMBER: 45-121

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:32000. Western Blot: No signal obtained yet but low background observed in Human Brain and Human Kidney lysates at up to 1ug/ml. We would appreciate any feedback from people in the field - have any results been reported with other antibodies/lysates?

IMMUNOGEN: PRDM10 antibody was raised against a 13 amino acid synthetic peptide near the C-Terminus of PRDM10.

HOST SPECIES: Goat

Properties

PURIFICATION: PRDM10 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: PRDM10 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: PRDM10, KIAA1231, PR domain containing 10, tristanin, PFM7, TRIS

ACCESSION NO.: NP_064613

PROTEIN GI NO.: 41349458

OFFICIAL SYMBOL: PRDM10

GENE ID: 56980

Background

REFERENCES: 1) Alvarez-Venegas R, Avramova Z. SET-domain proteins of the Su(var)3-9, E(z) and trithorax families. Gene. 2002 Feb 20;285(1-2):25-37. Review.

FOR RESEARCH USE ONLY

December 13, 2016