



## BS69 Antibody

CATALOG NUMBER: 45-344

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	ELISA, WB
<b>APPLICATIONS:</b>	ELISA: antibody detection limit dilution 1:32000. Western Blot: This antibody has been successfully used in Human Glioma lysates at various levels and no band was detected in normal brain lysates.
<b>SPECIFICITY:</b>	This antibody is expected to recognise all reported human isoforms (NP_006615.2; NP_997644.2; NP_001189393.1; NP_001189394.1; NP_001189395.1; NP_001189396.1; NP_001189397.1).
<b>IMMUNOGEN:</b>	BS69 antibody was raised against a 12 amino acid synthetic peptide near the N-Terminus of BS69.
<b>HOST SPECIES:</b>	Goat

### Properties

<b>PURIFICATION:</b>	BS69 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	BS69 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
<b>CONCENTRATION:</b>	500 ug/mL
<b>STORAGE CONDITIONS:</b>	Aliquot and store at -20°C. Minimize freezing and thawing.
<b>CLONALITY:</b>	Polyclonal
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	BS69, adenovirus 5 E1A binding protein, ZINC FINGER MYND DOMAIN-CONTAINING PROTEIN 11, ZMYND11, BS69
<b>ACCESSION NO.:</b>	NP_006615.1, NP_997644.1
<b>PROTEIN GI NO.:</b>	5729746
<b>OFFICIAL SYMBOL:</b>	ZMYND11
<b>GENE ID:</b>	10771

### Background

<b>REFERENCES:</b>	1) Hateboer G, Gennissen A, Ramos YF, Kerkhoven RM, Sonntag-Buck V, Stunnenberg HG, Bernards R. BS69, a novel adenovirus E1A-associated protein that inhibits E1A transactivation. EMBO J. 1995 Jul 3;14(13):3159-69.
--------------------	---

**FOR RESEARCH USE ONLY**