




CD177 Antibody [4C4]

CATALOG NUMBER: 51-762



Immunohistochemistry of human spleen tissue stained using CD177 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, IP, WB
APPLICATIONS:	CD177 antibody can be used in ELISA starting at 1 ug/mL, Western Blot starting at 1 ug/mL, and immunohistochemistry starting at 20 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	CD177 antibody can be stored short term 4 °C. For long term storage aliquot and store at -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CD177, CD177 molecule, CD177 antigen, Cell surface receptor, HNA-2a, HNA2A, NB1, PRV-1, Polycythemia rubra vera 1, PRV1, NB1 glycoprotein, NB1 GP
ACCESSION NO.:	Q8N6Q3
PROTEIN GI NO.:	91208246
OFFICIAL SYMBOL:	CD177
GENE ID:	57126

FOR RESEARCH USE ONLY

December 13, 2016