




NEUROD1 Antibody [3H8]

CATALOG NUMBER: 51-773



Immunohistochemistry of human testis
tissue stained using NEUROD1
Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	NEUROD1 antibody can be used in Western Blot starting at 2 ug/mL, immunohistochemistry starting at 10 ug/mL, immunoprecipitation starting at 2 ug/mL, and flow cytometry starting at 2 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	NEUROD1 antibody can be stored short term 4 °C. For long term storage aliquot and store at -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	NEUROD1, Beta2, BHF-1, NEUROD, Neurogenic differentiation 1, MODY6, NIDDM, BHLHa3, Neuronal differentiation 1
ACCESSION NO.:	Q13562
PROTEIN GI NO.:	311033428
OFFICIAL SYMBOL:	NEUROD1
GENE ID:	4760

FOR RESEARCH USE ONLY

December 13, 2016