



RFPL2 Antibody

CATALOG NUMBER: 46-286

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: Antibody detection limit dilution 16,000

SPECIFICITY: This is expected to recognize both RFPL2 (NP_006596) and RFPL3 (NP_006595), which are virtually identical.

IMMUNOGEN: RFPL2 antibody was raised against a 12 amino acid synthetic peptide near the C-Terminus of RFPL2.

HOST SPECIES: Goat

Properties

PURIFICATION: RFPL2 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: RFPL2 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: RFPL2, RNF79, ret finger protein-like 2, RFPL3, ret finger protein-like 3

ACCESSION NO.: NP_006596

PROTEIN GI NO.: 148728184

OFFICIAL SYMBOL: RFPL2

GENE ID: 10739; 10738

Background

REFERENCES: 1) Seroussi E, Kedra D, Pan HQ, Peyrard M, Schwartz C, Scambler P, Donnai D, Roe BA, Dumanski JP. Duplications on human chromosome 22 reveal a novel Ret Finger Protein-like gene family with sense and endogenous antisense transcripts. Genome Res. 1999 Sep;9(9):803-14.

FOR RESEARCH USE ONLY

December 13, 2016