



EBI3 Antibody

CATALOG NUMBER: 70-367

Specifications

SPECIES REACTIVITY:	Chimpanzee, Human
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	EBI3 Antibody can be used for Immunohistochemistry in paraffin embedded tissues starting at 1:100, and Western Blotting starting at 2 - 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	EBI3 is routinely seen in western blot at approximately 35 kD. The amino acid sequence used as immunogen is 100% homologous in human (isoform CRA_a and CRA_b),.
IMMUNOGEN:	A portion of amino acids 120-170 of human EBI3.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Protein G Column
BUFFER:	PBS, 0.05% BSA, 0.05% sodium azide
CONCENTRATION:	0.5 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	EBI3, Epstein-Barr virus induced 3, IL-27 subunit beta, IL27 subunit, IL27B, Interleukin-27 subunit beta, IL-27B, Cytokine receptor, EBV-induced gene 3 protein, IL35 subunit
ACCESSION NO.:	Q14213
PROTEIN GI NO.:	47605806
OFFICIAL SYMBOL:	EBI3
GENE ID:	10148

Background

FOR RESEARCH USE ONLY

December 13, 2016