



## VIM / Vimentin Antibody

CATALOG NUMBER: 70-375

### Specifications

<b>SPECIES REACTIVITY:</b>	Human, Mouse, Rat
<b>TESTED APPLICATIONS:</b>	IHC, WB
<b>APPLICATIONS:</b>	VIM / Vimentin Antibody can be used for Immunohistochemistry in paraffin embeded tissues starting at 1:100, and Western Blotting starting at 1:5000.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	Recombinant human protein purified from E. coli (His-Vimentin).
<b>HOST SPECIES:</b>	Rabbit

### Properties

<b>PURIFICATION:</b>	Affinity Purified
<b>BUFFER:</b>	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
<b>STORAGE CONDITIONS:</b>	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
<b>CLONALITY:</b>	Polyclonal
<b>ISOTYPE:</b>	IgG
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	VIM, Vimentin
<b>ACCESSION NO.:</b>	P08670
<b>PROTEIN GI NO.:</b>	55977767
<b>OFFICIAL SYMBOL:</b>	VIM
<b>GENE ID:</b>	7431

### Background

FOR RESEARCH USE ONLY

December 13, 2016