



prosci-inc.com



ProSci Incorporated
12170 Flint Place
Poway, CA 92064



Toll Free: +1 (888) 513 9525
Local: +1 (858) 513 2638
Fax: +1 (858) 513 2692

techsupport@prosci-inc.com

FOS / c-FOS Antibody

CATALOG NUMBER: 70-430

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ELISA, IHC-P (1:100), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Fos Antibody detects endogenous levels of total Fos protein.
IMMUNOGEN:	Synthetic peptide from human FOS.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	FOS, Activator protein 1, AP-1, Cellular oncogene c-fos, Cellular oncogene fos, Proto-oncogene c-Fos, v-fos, C-FOS, G0s7, p55
ACCESSION NO.:	P01100
PROTEIN GI NO.:	120470
OFFICIAL SYMBOL:	FOS
GENE ID:	2353

Background

FOR RESEARCH USE ONLY

December 13, 2016