



LY86 / MD-1 Antibody

CATALOG NUMBER: 70-601

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	IHC, IP, WB
APPLICATIONS:	LY86 / MD-1 Antibody can be used for Immunohistochemistry in paraffin embedded tissues starting at 10 ug/mL, and Immunoprecipitation starting at 2 ug/mL,
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	In Ramos, a 25 kD band is observed.
IMMUNOGEN:	A KLH-conjugated synthetic peptide corresponding to amino acids 112-125 of human MD-1.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Protein G Column
BUFFER:	PBS, 0.05% sodium azide.
CONCENTRATION:	0.5 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	LY86, DJ80N2.1, Ly-86, MD1, MD-1, MD-1, RP105-associated, MMD-1, Protein MD-1, RP1-80N2.1, Lymphocyte antigen 86
ACCESSION NO.:	O95711
PROTEIN GI NO.:	20138465
OFFICIAL SYMBOL:	LY86
GENE ID:	9450

Background

FOR RESEARCH USE ONLY

December 13, 2016