





## CD27 Antibody [LG.3A10] (FITC)

CATALOG NUMBER: 48-006



Human spleen tissue stained with CD27 Antibody at 10 ug/mL followed by biotinylated secondary antibody, alkaline phosphatase-streptavidin and chromogen.



Balb/c Thymocytes labelled with including isotypic control. Percentage of cells stained above control: 90%

### Specifications

<b>SPECIES REACTIVITY:</b>	Human, Mouse
<b>TESTED APPLICATIONS:</b>	FACS, IHC
<b>APPLICATIONS:</b>	CD27 antibody can be used in immunohistochemistry starting at 10 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	MCD27 tag expressing clones AR0524 and AR0530
<b>HOST SPECIES:</b>	Hamster

### Properties

<b>PURIFICATION:</b>	Protein G Column
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS, 0.02% sodium azide, EIA grade BSA.
<b>STORAGE CONDITIONS:</b>	Store CD27 antibody at 4 °C or -20 °C. As with all antibodies avoid freeze/thaw cycles.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG1
<b>CONJUGATE:</b>	FITC

### Additional Info

<b>ALTERNATE NAMES:</b>	CD27, CD27 antigen, CD27 molecule, S152, T14, T-cell activation antigen CD27, CD27L receptor, T cell activation antigen S152, TNFRSF7, Tp55
<b>ACCESSION NO.:</b>	P26842
<b>PROTEIN GI NO.:</b>	269849546
<b>OFFICIAL SYMBOL:</b>	CD27
<b>GENE ID:</b>	939

### Background

