





Catalase Antibody

CATALOG NUMBER: 48-667



Immunohistochemistry staining of Catalase in kidney tissue using Catalase Antibody.



Immunohistochemistry staining of Catalase in liver using Catalase Antibody.

Specifications

SPECIES REACTIVITY:	Bovine, Human
TESTED APPLICATIONS:	ELISA, IF, IHC, IP, WB
APPLICATIONS:	Catalase antibody can be used in ELISA, and immunohistochemistry starting at 1 - 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Catalase antibody was raised against Catalase from bovine liver (Bovine).
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	IgG Fractionation
PHYSICAL STATE:	Lyophilized
BUFFER:	0.02 M Potassium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 0.01% (w/v) Sodium Azide
STORAGE CONDITIONS:	Store Catalase antibody at 4 °C or -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CAT, Catalase
ACCESSION NO.:	P04040
PROTEIN GI NO.:	115702
OFFICIAL SYMBOL:	CAT
GENE ID:	847

Background

FOR RESEARCH USE ONLY

