




Noggin Antibody

CATALOG NUMBER: 49-860



Immunohistochemistry staining of Noggin
in cerebellum tissue using Noggin
Antibody.

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	Noggin antibody can be used in immunohistochemistry starting at 7 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Noggin antibody was raised against an internal peptide of Noggin (Human).
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 0.02% sodium azide.
STORAGE CONDITIONS:	Noggin antibody should be stored long term (months) at -20 °C and short term (weeks) at 4 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	NOG, Symphalangism 1 (proximal), SYNS1, SYM1, Noggin
ACCESSION NO.:	Q13253
PROTEIN GI NO.:	15214099
OFFICIAL SYMBOL:	NOG
GENE ID:	9241

Background

