




CD73 Antibody [1D7]

CATALOG NUMBER: 51-319



Immunohistochemistry of human liver tissue stained using CD73 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC
APPLICATIONS:	CD73 antibody can be used in ELISA starting at 1:000 - 1:1000, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein encoding a fragment of human NT5E.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Ascites
PHYSICAL STATE:	Liquid
BUFFER:	0.03% sodium azide
STORAGE CONDITIONS:	CD73 antibody should be stored long term (months) at -20 °C and short term (weeks) at 4 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	NT5E, 5-nucleotidase, ecto (CD73), 5'-nucleotidase, 5 nucleotidase (CD73), 5-NT, 5-nucleotidase, 5'-nucleotidase, ecto (CD73), CD73, CD73 antigen, E5NT, Ecto-5-nucleotidase, ENT, EN, NT, Purine 5-Prime-Nucleotidase, NT5, NTE
ACCESSION NO.:	P21589
PROTEIN GI NO.:	112825
OFFICIAL SYMBOL:	NT5E
GENE ID:	4907

FOR RESEARCH USE ONLY

December 13, 2016