




SNRPA Antibody [3F9-1F7]

CATALOG NUMBER: 51-512



Immunohistochemistry of human small intestine, submucosal plexus stained using SNRPA Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	SNRPA antibody can be used in Western Blot, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	SNRPA (AAH00405, 1 a.a. ~ 283 a.a) full length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.4. Sourced in Ascites.
STORAGE CONDITIONS:	Store SNRPA antibody at -20 °C. Aliquot to avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	SNRPA, U1A, Mud1, U1 snRNP A, U1 snRNP-specific protein A, U1-A
ACCESSION NO.:	P09012
PROTEIN GI NO.:	134092
OFFICIAL SYMBOL:	SNRPA
GENE ID:	6626

Background

