




IKK Gamma Antibody [46B844]

CATALOG NUMBER: 51-624



Immunohistochemistry of human placenta
tissue stained using IKK Gamma
Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	FACS, IHC, WB
APPLICATIONS:	IKK Gamma antibody can be used in ELISA, Western Blot starting at 1 ug/mL, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	A 48 kD band is observed.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein G Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 0.2% gelatin, 0.05% sodium azide.
STORAGE CONDITIONS:	IKK Gamma antibody can be stored short term 4 °C. For long term storage aliquot and store at -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	IKBKG, AMCBX1, FIP3, Fip3p, IkappaB kinase gamma, IKKgamma, IKK-gamma, NEMO, NF-kappa-B essential modifier, I-kappa-B kinase gamma-subunit, I-kappa-B kinase subunit gamma, Ikb kinase gamma subunit, IKKAP1, Incontinentia pigmenti, IP2, IPD2, NF-kappa-B essential modulator, ZC2HC9, FIP-3, Ikb kinase subunit gamma, IKKG, IP1, NFkappaB essential modulator
ACCESSION NO.:	Q9Y6K9
PROTEIN GI NO.:	6685695

OFFICIAL SYMBOL: IKBKG

GENE ID: 8517

Background

FOR RESEARCH USE ONLY

December 13, 2016