




CD44 Antibody [SPM521]

CATALOG NUMBER: 51-648



Immunohistochemistry of human spleen tissue stained using CD44 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IHC
APPLICATIONS:	CD44 antibody can be used in Western Blot, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Do not freeze
IMMUNOGEN:	Synthetic peptide corresponding to human CD44
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	10 mM PBS, pH 7.4, BSA, sodium azide.
STORAGE CONDITIONS:	Store CD44 antibody at 2 °C to 8 °C degrees. Do not freeze.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CD44, CDW44, CD44 antigen, Cell surface glycoprotein CD44, CSPG8, ECMR-III, Epican, HUTCH-I, LHR, MDU2, MC56, MIC4, Hermes antigen, Hyaluronate receptor, Phagocytic glycoprotein 1, PGP-1, PGP-I, Pgp1, Phagocytic glycoprotein I, MDU3, CD44R, HCELL, Heparan sulfate proteoglycan
ACCESSION NO.:	P16070
PROTEIN GI NO.:	308153615
OFFICIAL SYMBOL:	CD44
GENE ID:	960

Background

