



DBI Antibody [27C9]

CATALOG NUMBER: 70-091

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, IP, WB
APPLICATIONS:	DBI Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 1:200 and Western Blot starting at 1:100 - 1:500.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant human GST-fusion protein purified from E. coli.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Ammonium Sulfate Precipitation
PHYSICAL STATE:	Liquid
BUFFER:	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
STORAGE CONDITIONS:	DBI Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles. Store undiluted.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2b,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	DBI, ACBP, Acyl-CoA-binding protein, CCK-RP, Diazepam-binding inhibitor, ACBD1, GABA receptor modulator, EP, Endozepine
ACCESSION NO.:	P07108
PROTEIN GI NO.:	118276
OFFICIAL SYMBOL:	DBI
GENE ID:	1622

Background

FOR RESEARCH USE ONLY

December 13, 2016