



MET Antibody [4AT44]

CATALOG NUMBER: 70-096

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	MET Monoclonal Antibody can be used for ELISA starting at 1:1000, immunohistochemistry (tested on paraffin embedded tissues) starting at 10 ug/mL and Western Blot starting at 1:100 - 1:500.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Purified recombinant protein encoding the catalytic domain of human Met.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein G Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 0.09% sodium azide
STORAGE CONDITIONS:	MET Monoclonal antibody may be stored at Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	MET, AUTS9, C-Met, HGF/SF receptor, HGFR, Met kinase, Proto-oncogene c-Met, Scatter factor receptor, SF receptor, HGF receptor, RCCP2, Tyrosine-protein kinase Met
ACCESSION NO.:	P08581
PROTEIN GI NO.:	251757497
OFFICIAL SYMBOL:	MET
GENE ID:	4233

Background

FOR RESEARCH USE ONLY

December 13, 2016